

Technical Parameter

Item	SK-8000A	SK-8000C	SK-8000B
Visual field range	133°		
Minimum pupil	6mm		
Collector	Medical-grade professional CMOS		
Pixel	≥800 million		
Light source adjustment	Seamless adjustment light		
Lighting Method	Built-in integrated lighting		
Shooting Method	Foot shooting,software shooting		
Focus mode	Manual Focus	Auto focus	
Lesion marking	Manual marking	Auto marking	
Shooting mode	Colour photography	Colour photography+Fluorography	
Port	USB, DICOM		

WIDE FIELD RETINA CAMERA SK-8000



DITY

Optical

flexible solutions you can trust

www.dty.co.il - 03-9341133 - 052-3270220 - ד"ר שרית אופטיקה

SPECIALIST PAEDIATRIC
FUNDUS IMAGING SYSTEM



Tel:+86 23 68643990
 URL:en.cqsunkingdom.com
 E-mail:sales@cqsunkingdom.com
 Add:Room12,Floor10,Block A of China Resource Center.
 Jiulongpo District,Chongqing 400050,China.