

New Standard!

AUTO LENSMETER

GL-7000


GL-7000B

NEW



Grand Seiko Co., Ltd.

Ergonomic Design



Proposing the New Style Pursued the Ease of Use! Designed to be much simpler to use and see based on the human engineering.

Color LCD


With the Color LCD Monitor and Icon, the information is easy to understand.

Easy Measurement of Progressive Lens

Due to the automatic recognition of progressive lens and other features, all the lens can be measured much more comfortably.

Automatic Recognition of Progressive Lens

When set a progressive lens, it will be automatically recognized, and the display will be changed for the measurement of a progressive lens.



Printer (GL-7000 Only)

With the high speed Thermal Printer, it can print out the measured data quickly. Additionally, it can also print out the progressive lens graph.

Lens Plate

No need to adjust the Lens Plate while setting a lens. Press the "PUSH" Mark on the Plate, and it will come out automatically.

Selection of Abbe Number


By choosing from the 5 different numbers, even the Ultra Hi Index Lens can be measured correctly.

GL-7000B

The economical model without printer for those of you who do not require print-out.

Color LCD Display

With the use of Color LCD Monitor, the measured information can be distinguished easily. Furthermore, due to the use of Icon, even the inexperienced operator can use it comfortably.



Specification

Measurement Range	Sphere (S)	-25~+25D (0.01/0.12/0.25Dstep)
	Cylinder (C)	0~±10D (0.01/0.12/0.25Dstep)
	Axis (A)	1~180° (1°step)
	Addition	0~+10D (0.01/0.12/0.25Dstep)
	Prism	0~10△ (0.01/0.12/0.25△step)
Wavelength	660nm	
Lens	Glasses Lens, Hard/Soft Contact Lens	
Lens Size	Maxφ100mm	
Monitor	5.7 inch LCD Monitor (Color)	
Printer	Thermal Printer (Width58mm) [GL-7000 Only]	
Dimension	(W) 200mm× (D) 395mm× (H) 365mm	
Weight	About 6kg	
Output	RS-232C Interface	
Power Supply	100~240V 50/60Hz	
Consumption	40VA	
Power Save	OFF, 3, 5, 10min. (Selectable)	

- Specifications and design are subject to change without prior notice for improvement.
- The part of screen is composed photograph.
- The color of instrument on the catalogue and the real product might be different.

CAUTION For the proper and safety use, please read the Instruction Manual thoroughly before using the product.

HIGH-TECH
HIGH-TOUCH
HIGH-IDEALS
RyuSyo
RyuSyo Industrial Co., Ltd.

2-1-8 Minami-honmachi, Chuo-ku, Osaka/Japan 541-0054



Grand Seiko Co., Ltd.

Head Office & Plant
12-19, Kashima, Fukuyama, Hiroshima 720-0091 Japan
Tel.*81-84-952-2151 Fax.*81-84-951-9456
<http://www.grandseiko.com>

חברת מייצגת:

ד.ט.י. שותף אופטיקה בע"מ
ציוד אופטלי ורפואי